

MECONTROL

	Sensor type:	UBC sensor	UBC XT sensor
١	Measurement principle:	microwave	microwave and nucleonic
	Measurement range:	0 – 40 % carbon in fly ash	0 – 40 % carbon in fly ash
	Measurement accuracy:	+/- 0,6 % based on 1 sigma (0 -10 %)	+/- 0,3 % based on 1 sigma (0 -10 %)
	Materials:	steel probe with hardened ash auger	steel probe with hardened ash auger
	Measuring cycle:	2 – 10 minutes (depending on ash flow)	2 – 10 minutes (depending on ash flow)
	Process temperature:	0 – 150 °C (32 – 300 °F)	0 – 150 °C (32 – 300 °F)
	Pressure:	- 30 mbar – 0 mbar	- 30 mbar - 0 mbar
	Dimensions:	screw insert depth: 300 mm, outside length of shaft and motor: 600 mm	screw insert depth: 300 mm, outside length of shaft and motor: 600 mm
	Air consumption:	201/h@min 3 bar	201/h@min 3 bar
	Degree of protection:	IP 55, NEMA 12 Cabinet	IP 55, NEMA 12
	Number of channels:	4/6/8	4/6/8
	Degree of protection:	IP 55, NEMA 12 (IP 66, NEMA 4, upon request)	
	Temperature range:	0 – 55 °C (32 – 130 °F)	
	Dimensions:	4/6/8 channels: width 800/800/1000 mm, depth 600 mm, height 2000 mm + socket	
	Maximum cable length to sensors:	190 m	
	Power supply:	1 x 230/110 VAC (L, N, PE), 50/60 Hz or 3 x 400 VAC (L1, L2, L3, N, PE)	
	Signal output:	4 – 20 mA	
	Remote access:	via modem/internet connection	
	Data collection and export via phone line/internet possible. Complete remote access and control!		

Technical Changes Reserved

For further information please contact:

PROMECON

Phone +49 (0)39203 512-0 Fax +49 (0)39203 512-202 D-39179 Barleben www.promecon.com info@promecon.com

MECONTROL UBC MECONTROL UBC XT

Your complete fly ash assessment online!





MECONTROL UBC MECONTROL UBC XT

Your complete fly ash assessment online!

Online UBC sensor


Microwave resonance measurement with patented sample collection and treatment: The most commonly used UBC online sensor worldwide.



Online UBC sensor on an ash bunker.

Online UBC XT sensor

MECONTROL UBC XT measurement provides lab accuracy online in your process.



Accuracy process versus laboratory $\sigma = 0.19\%$

Get deep insight into your combustion and fly ash production process and find answers you always wanted to know:

Does your ash have the right size distribution, the right unburned carbon loss

What is your boiler's reaction to coal type changes

How far can you adjust O_2 setting in respect to ash quality

Does your mill need maintenance

Get the answers dynamically online!

The MECONTROL UBC / MECONTROL UBC XT central measurement base station controls all sensors and collates data.

The following capabilities are provided:

- Full SCADA package (optional)
- Digital as well as analogue I/O
- I Full access via modem/internet/ethernet
- Large data storage capacity for months of online data logging
- Inputs available for external signals: release signal 24 VDC
- Panel IP 66 rated (optional)

